



Hexagon head bolt ISO 4014
Steel Zinc plated 8.8 M4X25

Article number	01200.040.025
Brand	-
UBB	950351140245
UNSPSC	31161620
EAN	8715492024657
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	25 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4014
ASME	B18.2.3.1M
NEN	1555
DIN	931
NF	E25-112

Technical Specification

b (min.): L≤125mm	14
d-D	M4
k	2.8
L (mm)	25
P	0.7
s	7

Technical Drawing

