



## Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M4X35

|                |               |
|----------------|---------------|
| Article number | 01200.040.035 |
| Brand          | -             |
| UBB            | 951351616937  |
| UNSPSC         | 31161620      |
| EAN            | 8715492024671 |
| PKG. of 500    | Full Box Only |

### Technical Parameters

|                   |               |
|-------------------|---------------|
| Diameter          | M4            |
| Length            | 35 mm         |
| Class             | 8.8           |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Zinc plated   |
| Thread            | Metric thread |

### Standards

|      |            |
|------|------------|
| DIN  | 931        |
| NF   | E25-112    |
| NEN  | 1555       |
| ASME | B18.2.3.1M |
| ISO  | 4014       |

### Technical Specification

|                   |     |
|-------------------|-----|
| b (min.): L≤125mm | 14  |
| d-D               | M4  |
| k                 | 2.8 |
| L (mm)            | 35  |
| P                 | 0.7 |
| s                 | 7   |

### Technical Drawing

