



Hexagon head bolt ISO 4014
Steel Zinc plated 8.8 M4X50

Article number	01200.040.050
Brand	-
UBB	950351140575
UNSPSC	31161620
EAN	8715492024701
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
DIN	931
NEN	1555
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): L≤125mm	14
d-D	M4
k	2.8
L (mm)	50
P	0.7
s	7

Technical Drawing

