

Hexagon nut DIN 934 Steel
Zinc plated |8| M12

Article number	01300.120.001
Brand	-
UBB	950355012614
UNSPSC	31161727
EAN	8715492042118
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	1560
NF	E25-401
DIN	934

Technical Specification

d-D	M12
m	10
P	1.75
s	19

Technical Drawing

