



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M3X10

Article number	07160.030.010
Brand	-
UBB	950351440884
UNSPSC	31161605
EAN	8715492070760
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	10 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4762
BS	4168-1
NF	E25-125
NEN	1241
ASME	B18.3.1M
DIN	912

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if $L \leq$	20
k (max.)	3
L (mm)	10
P	0.5
s	2.5

Technical Drawing

