



## Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M3X12

|                |               |
|----------------|---------------|
| Article number | 07160.030.012 |
| Brand          | -             |
| UBB            | 950351440967  |
| UNSPSC         | 31161605      |
| EAN            | 8715492070777 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                   |                  |
|-------------------|------------------|
| Diameter          | M3               |
| Length            | 12 mm            |
| Class             | 8.8              |
| Driving features  | Hexagon socket   |
| Head shape        | Cylindrical head |
| Material          | Steel            |
| Thread direction  | Right            |
| Surface treatment | Zinc plated      |
| Thread            | Metric thread    |

### Standards

|      |          |
|------|----------|
| NEN  | 1241     |
| DIN  | 912      |
| ASME | B18.3.1M |
| BS   | 4168-1   |
| NF   | E25-125  |
| ISO  | 4762     |

### Technical Specification

|                    |     |
|--------------------|-----|
| b                  | 18  |
| d-D                | M3  |
| dk (max.)          | 5.5 |
| Full thread if L ≤ | 20  |
| k (max.)           | 3   |
| L (mm)             | 12  |
| P                  | 0.5 |
| s                  | 2.5 |

### Technical Drawing

