



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M3X14

Article number	07160.030.014
Brand	-
UBB	500645092890
UNSPSC	31161605
EAN	8717077059160
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	14 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.3.1M
NEN	1241
DIN	912
BS	4168-1
NF	E25-125
ISO	4762

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if $L \leq$	20
k (max.)	3
L (mm)	14
P	0.5
s	2.5

Technical Drawing

