



Hexagon thin nut, turned DIN 439 2 Free-cutting steel Zinc plated with thick Cr(III) passivation 04 turned M16

Article number	11355.160.001
Brand	-
UBB	500647853844
UNSPSC	31161727
EAN	8717077275133
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M16
Class	04
Driving features	Hexagon
Material	Free-cutting steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread
Info	turned

Standards

ISO	4035
NEN	2334-B
ASME	B18.2.4.5M
NF	E25-405-1
DIN	439-2

Technical Specification

d-D	M16
m	8
P	2
s	24

Technical Drawing

