

Slotted round nut for hook spanners MF DIN 1804 W Steel Plain 04 turned M8X1,00

Article number	11571.080.100
Brand	-
UBB	500648361128
UNSPSC	31161727
EAN	8717077215641
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M8
Brand	Fabory
Class	040
Driving features	Slotted
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread
Info	Slotted round nuts for hookspanners when combined with internal tab washers according to DIN 462 provide mechanical locking.They are easily assembled with a hook wrench (hook spanner) e.g. to DIN 1810.turn

Standards

DIN	1804-W
-----	--------

Technical Specification

b	4
d-D	M8
d2 (h11)	20
h (h14)	5

Technical Drawing

Number of slots	4
Part number	P1
Wall thickness t	1.5

FABORY

