



Prevailing torque type hexagonal thin nut with non- metallic insert ISO 10511 Steel Zinc plated with thick Cr(III) passivation 04 M10

Article number	12305.100.001
Brand	-
UBB	500650967168
UNSPSC	31162400
EAN	8717077311244
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M10
Class	04
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

ISO	10511
-----	-------

Technical Specification

d-D	M10
h (max.)	8.56
P	1.5
s	16

Technical Drawing

