



Prevailing torque type hexagon nut with plastic insert, high type ISO 7040 Steel Zinc plated 10 M24

Article number	12515.240.001
Brand	-
UBB	500650980922
UNSPSC	31162400
EAN	8717077312623
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M24
Class	10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	7040
DIN	6924

Technical Specification

d-D	M24
h (max.)	27.1
P	3
s	36

Technical Drawing

