



**Threaded rod length 1 metre
DIN 976-1A Steel Zinc plated
8.8 M12**

Article number	20230.120.001
Brand	-
UBB	950353012749
UNSPSC	31161618
EAN	8715492605832
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M12
Length	1000 mm
Class	8.8
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	1 meter

Standards

NF	E25-136
DIN	976-1A

Technical Specification

d-D	M12
L (mm)	1000
P	1.75

Technical Drawing

