



**Threaded rod DIN 976-1A
Zinc Plated with CR(III)
Passivation 4.8 1 mtr M10**

Article number	20303.100.001
Brand	-
UBB	500648193166
UNSPSC	31161618
EAN	8717077218161
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	1000 mm
Class	4.8
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread
Info	1 meter

Standards

DIN	976-1A
NF	E25-136

Technical Specification

d-D	M10
L (mm)	1000
P	1.5

Technical Drawing

