

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M2X8



Article number 24665.020.008

Brand -

UBB 950353904184

UNSPSC 31161504

EAN 8715492640536

PKG. of 200 Full Box Only

Technical Parameters

Diameter (d-D)	M2
Length (L) (mm)	8
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	7045-H
DIN	7985-H

Technical Specification

Thread length (min.)	16
d_k (max.)	4
Full thread if $L \leq$	18
k	1.6
No. cross recess	1
P	0.40

Technical Drawing

