



## Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M2,5X8

Article number	24665.025.008
Brand	-
UBB	950353904671
UNSPSC	31161504
EAN	8715492640581
PKG. of 200	Full Box Only

### Technical Parameters

Diameter	M2.5
Length	8 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

DIN	7985
ISO	≈7045

### Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	5
Full thread if $L \leq$	20
k	2
L (mm)	8
No. cross recess	1
P	0.45

### Technical Drawing

