



**Slotted cheesehead din  
7513b DIN 7513 B Steel Zinc  
plated M4X10**

Article number	27030.040.010
Brand	-
UBB	500651087503
UNSPSC	31162400
EAN	8717077323216
PKG. of 1000	Full Box Only

**Technical Parameters**

Diameter	M4
Length	10 mm
Driving features	Slotted
Head shape	Round head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info	The predrill diameterter Drill ø (H11) is a guideline for medium strength material. For soft or thin materials a smaller hole can be chosen, for hard or thick material a bigger hole may be chosen. It is recommended to select the exact diameter based on tests.The engagemnt depth should by no means exceed twice the nominal screw diameterter.
------	---

**Standards**

DIN	7513-BE
-----	---------

Technical Specification

d-D	M4
dk	7
k	2.6
L (mm)	10
n	1.2
P	0.7
t	1.1

Technical Drawing

