



**Slotted cheesehead din  
7513b DIN 7513 B Steel Zinc  
plated M4X10**

Article number	27030.040.010
Brand	-
UBB	500651087503
UNSPSC	31162400
EAN	8717077323216
PKG. of 1000	Full Box Only

**Technical Parameters**

Diameter	M4
Length	10 mm
Brand	Fabory
Driving features	Slotted
Head shape	Round head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info      The predrill diameterter Drill ø (H11) is a guideline for medium strength material. For soft or thin materials a smaller hole can be chosen, for hard or thick material a bigger hole may be chosen. It is recommended to select the exact diameter based on tests.The engagement depth should by no means exceed twice the nominal screw diameterter.

**Standards**

DIN	7513-BE
-----	---------

Technical Specification

d-D	M4
dk	7
k	2.6
L (mm)	10
n	1.2
P	0.7
Wall thickness t	1.1

Technical Drawing

