

MONOBOLT Countersunk head open end blind rivet, high strength 6,4X12,07MM (a)



Article number	34501.064.012
Brand	-
UBB	500682639587
UNSPSC	31162400
EAN	8717077782990
PKG. of 1500	Full Box Only

Technical Parameters

Mandrel material	Stainless steel
Clamping range (max.)	12.07
Head shape	Countersunk head
Material body/mandrel	Stainless steel A2 / Stainless steel A2

Standards

Technical Specification

B (min.)	10.03
D1 (max.)	2.4
Grip range	3.17-12.07
Hole ø (mm)	6.6
M	26.4
Shear strength, typical (kN)	11.78
T (min.)	12.19
Tensile strength, typical (kN)	10.45

Technical Drawing

