



Slotted raised countersunk head screw DIN 964 Brass CU2/CU3 Chrome plated M5X30

Article number 48571.050.030

Brand -

UBB 500648265923

UNSPSC 31161504

EAN 8717077230842

PKG. of 200 Full Box Only

Technical Parameters

Diameter	M5
Length	30 mm
Driving features	Slotted
Head shape	Countersunk oval head
Material	Brass
Material technical	CU2/CU3
Surface treatment	Chrome plated
Thread	Metric thread

Standards

ISO	≈2010
ASME	≈B18.6.7M
NF	≈E25-124
DIN	964
NEN	≈2371
BS	≈4183

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
f ≈	1.25
Full thread if L ≤	30
k (max.)	2.5
L (mm)	30
n	1.2
P	0.8
t (min.)	2

Technical Drawing

