

Slotted raised countersunk head screw ISO 2010 Brass CU2/CU3 Nickel plated M5X30



Artikelnummer	48575.050.030
Marke	-
UBB	500651147331
UNSPSC	31162400
EAN	8717077329195
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Diameter	M5
Length	30 mm
Driving features	Slotted
Head shape	Countersunk oval head
Material	Brass
Material technical	CU2/CU3
Thread direction	Right
Surface treatment	Nickel plated
Thread	Metric thread

Standards

ISO	2010
-----	------

Technische Spezifikation

d-D	M5
Thread length (min.)	38
dk (max.)	9.3
f ≈	1.2
Full thread if L ≤	45
k (max.)	2.7
L (mm)	30
n	1.2
P	0.8
t (min.)	2

Technische Zeichnung

