



Hexagon nut DIN 934 Stainless steel A2 70 M3

Article number	51080.030.001
Brand	-
UBB	950355217494
UNSPSC	31161727
EAN	8715492267320
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NEN	1560
NF	E25-401
DIN	934

Technical Specification

d-D	M3
m	2.4
P	0.5
s	5.5

Technical Drawing

