


Cladding screw/Hi-Lo thread/
center point Stainless steel
A2 50 ST5,5X45X30MM



Article number	51799.055.045
Brand	-
UBB	500634599996
UNSPSC	31162400
EAN	8717077007499
PKG. of 100	Full Box Only

Technical Parameters

Diameter	5.5 mm
Length	45 mm
Class	50
Driving features	Phillips
Head shape	Capping head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

Technical Specification

b	30
D (mm)	5.5
dk	9.2
k	3
L (mm)	45

Technical Drawing

