

Hexagon nut with serrated flange DIN ≈6923 Stainless steel A4 80 M8

Article number	53119.080.001
Brand	-
UBB	500571875987
UNSPSC	31161727
EAN	8715494272506
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Brand	Fabory
Class	80
Driving features	Hexagon
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standards

NF	≈E25-406
ISO	≈4161
DIN	≈6923

Info	Specific features of hexagon nuts with serrated flange:The flange enables built up forces under the nut to be spread over a larger area, consequently resulting in lower surface pressure.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.The serrated flange provides an excellent self-locking effect.
------	--

Technical Specification

d-D	M8
dc (max.)	17.9
m (max.)	8
P	1.25
s	13

Technical Drawing

