



YOKO DIE GRINDER MG-OA
240W 24000PMIN

Article number	E2022.000.105
Brand	-
UBB	500504316216
UNSPSC	31191603
EAN	8717981000135
PKG. of 1	Full Box Only

Technical Parameters

Rotational speed	25000
Max. operation pressure	6.3
Air inlet device-sided	R 1/4 inch
Air volume required	372

Standards