



**DIE GRINDER 33000 RPM
MG-OC**

Article number	MG-OCYOK
Brand	-
UBB	500619057796
UNSPSC	31191603
EAN	8717981064724
PKG. of 1	Full Box Only

Technical Parameters

Rotational speed	33000
Max. operation pressure	6.3
Air inlet device-sided	Other
Air volume required	180

Standards