

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name: Goldfresh geurstrips**
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Dreumex B.V.
Dommelstraat 1
5347 JK, Oss, The Netherlands
Postal box 681, 5340 AR, Oss, The Netherlands
Tel: +31 (0)412-406 506
Fax : +31 (0)412-406 509
E-mail address: mail@dreumex.com
Website: www.dreumex.com
- **1.4 Emergency telephone number:** Dreumex B.V. +31 (0)412-406 506

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS07

- Acute Tox. 4 H302 Harmful if swallowed.
 Skin Irrit. 2 H315 Causes skin irritation.
 Eye Irrit. 2 H319 Causes serious eye irritation.
 STOT SE 3 H335 May cause respiratory irritation.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms** GHS07
- **Signal word** Warning
- **Hazard-determining components of labelling:**
Fragrance Goldfresh
- **Hazard statements**
H302 Harmful if swallowed.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.
- **Precautionary statements**

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P103	Read label before use.
P261	Avoid breathing dust/fume/gas/mist/vapours/spray.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P264	Wash thoroughly after handling.
P270	Do not eat, drink or smoke when using this product.
P271	Use only outdoors or in a well-ventilated area.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

(Contd. on page 2)

Trade name: Goldfresh geurstrips

(Contd. of page 1)


P321	Specific treatment (see on this label).
P301+P312	IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P332+P313	If skin irritation occurs: Get medical advice/attention.
P337+P313	If eye irritation persists: Get medical advice/attention.
P330	Rinse mouth.
P302+P352	IF ON SKIN: Wash with plenty of water.
P362+P364	Take off contaminated clothing and wash it before reuse.
P405	Store locked up.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P501	Dispose of contents/container in accordance with local/regional/national/international regulations.

- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Chemical characterisation: Mixtures**
- **Description:** Mixture of substances listed below with nonhazardous additions.

Dangerous components:

Fragrance Goldfresh	2.5-10%
 Acute Tox. 4, H302; Skin Irrit. 2, H315; Eye Irrit. 2, H319; STOT SE 3, H335	

- **Additional information:** For the wording of the listed risk phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:**
 Rinse out mouth.
 Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
 No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
 No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
 CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture**
 No further relevant information available.

(Contd. on page 3)

Trade name: Goldfresh geurstrips

(Contd. of page 2)

- **5.3 Advice for firefighters**
- **Protective equipment:** In case of insufficient ventilation, wear suitable respiratory equipment.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures** Not required.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** No special precautions are necessary if used correctly.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:** Wash hands before breaks and at the end of work.
- **Respiratory protection:** Not required.
- **Protection of hands:**
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**

(Contd. on page 4)

Trade name: Goldfresh geurstrips

(Contd. of page 3)

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **Eye protection:** Goggles recommended during refilling

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form:	Solid
Colour:	Colourless
Odour:	Characteristic
Odour threshold:	Not determined.

· pH-value:	Not determined.
-------------	-----------------

· **Change in condition**

Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	Undetermined.

· Flash point:	Not applicable.
----------------	-----------------

· Flammability (solid, gaseous):	Not applicable.
----------------------------------	-----------------

· **Ignition temperature:**

Decomposition temperature:	Not determined.
----------------------------	-----------------

· Self-igniting:	Product is not selfigniting.
------------------	------------------------------

· Danger of explosion:	Product does not present an explosion hazard.
------------------------	---

· **Explosion limits:**

Lower:	Not determined.
Upper:	Not determined.

· Vapour pressure:	Not determined.
--------------------	-----------------

· Density:	Not determined.
------------	-----------------

· Relative density	Not determined.
--------------------	-----------------

· Vapour density	Not determined.
------------------	-----------------

· Evaporation rate	Not determined.
--------------------	-----------------

· **Solubility in / Miscibility with water:**

Not miscible or difficult to mix.

· Partition coefficient (n-octanol/water):	Not determined.
--	-----------------

· **Viscosity:**

Dynamic:	Not determined.
Kinematic:	Not determined.

(Contd. on page 5)

Trade name: Goldfresh geurstrips

(Contd. of page 4)

- **Solvent content:**
- **Organic solvents:** 0.0 %
- **9.2 Other information** No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity**
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity**
- **Primary irritant effect:**
- **Skin corrosion/irritation** No irritant effect.
- **Serious eye damage/irritation** No irritating effect.
- **Respiratory or skin sensitisation** No sensitising effects known.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation** Disposal must be made according to official regulations.

(Contd. on page 6)

Printing date 06.08.2015

Version number 1

Revision: 06.08.2015

Trade name: Goldfresh geurstrips

(Contd. of page 5)

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

· 14.1 UN-Number	
· ADR, ADN, IMDG, IATA	Void
· 14.2 UN proper shipping name	
· ADR, ADN, IMDG, IATA	Void
· 14.3 Transport hazard class(es)	
· ADR, ADN, IMDG, IATA	
· Class	Void
· 14.4 Packing group	
· ADR, IMDG, IATA	Void
· 14.5 Environmental hazards:	
· Marine pollutant:	No
· 14.6 Special precautions for user	Not applicable.
· 14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable.
· Transport/Additional information:	Not dangerous according to the above specifications.
· UN "Model Regulation":	-

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
No further relevant information available.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H302 Harmful if swallowed.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.

· Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals

(Contd. on page 7)

GB

**Safety data sheet
according to 1907/2006/EC, Article 31**



Printing date 06.08.2015

Version number 1

Revision: 06.08.2015

Trade name: Goldfresh geurstrips

(Contd. of page 6)

EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
Acute Tox. 4: Acute toxicity, Hazard Category 4
Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2
Eye Irrit. 2: Serious eye damage/eye irritation, Hazard Category 2
STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3

· *** Data compared to the previous version altered.**

— GB —