FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M3X4

Article number	07160.030.004
Brand	-
UBB	500645092718
UNSPSC	31161605
EAN	8717077059153
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	4 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-125
ASME	B18.3.1M
BS	4168-1
DIN	912
ISO	4762
NEN	1241

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if L ≤	20
k (max.)	3
L (mm)	4
P	0.5
s	2.5

Technical Drawing

