
FABORY



Cross recessed countersunk head screw for chipboard Pozidriv Steel Zinc plated 3X25MM

Article number	29240.030.025
Brand	-
UBB	950350028805
UNSPSC	31161508
EAN	8715492952493
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3 mm
Length	25 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Info	All dimensions are guide values and may deviate dependent on the manufacturer.Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

Technical Specification

D (mm)	3
dk (max.)	5.9
k (max.)	1.9
L (mm)	25
No. cross recess	1

Technical Drawing

