

## Self-clinching blind stand off Stainless steel A1 M4X7,10X8X4

Article number	51227.040.008
Brand	-
UBB	500656767562
UNSPSC	31161816
EAN	8712423021952
PKG. of 1000	Full Box Only

### Technical Parameters


Diameter	M4
Length	8 mm
Material	Stainless steel
Material technical	A1
Thread direction	Right
Thread	Metric thread
Info	Steel self-clinching blind stand offs are suitable for use in steel sheet with a maximum hardness of HRB70. For steel sheets with higher hardnesses, rivet bushes are recommended.

### Standards

### Technical Specification

B (min.)	4
C	7.1
d-D	M4
Hole size	7.2
L (mm)	8
Min. distance sheet edge	8

### Technical Drawing



Min. recommended sheet thickness	1.3
-------------------------------------	-----

S	7.9
---	-----

ADUK